


How to Measure Your Screen

It is critical that you measure your monitor screen correctly to ensure proper fit of your computer filter.

Be sure to measure only the viewable screen area.

Order the Correct 3M™ Privacy Filter

Choose from widescreen or standard size to assure the correct fit for your notebook or LCD monitor.



For frameless filters, the size must be exactly what you measure. For framed filters, choose the size that is nearest to your actual screen measurement or slightly larger.

3M™ Notebook/LCD Privacy Filters	Filter Viewing Area Height x Width	Filter Viewing Area Diagonal	Fits Monitor Size
PF8.9W	4-7/16" x 7-11/16"	8-7/8"	8.9" Widescreen
PF10.1W	5-1/16" x 8-3/4"	10-1/16"	10.1" Widescreen
PF12.1	7-3/8" x 9-3/4"	12-1/16"	12.1"
PF12.1W	6-1/2" x 10-3/8"	12/1/16"	12.1" Widescreen
PF13.3	8.0" x 10-5/8"	13-1/4"	13.3"
PF13.3W	7-15/16" x 10-5/8"	13-5/16"	13.3" Widescreen
PF14.0W	6-7/8" x 12-3/16"	14"	14.0" Widescreen
PF14.1	8-1/2" x 11-1/4"	14-1/16"	14.1"
PF14.1W	7-1/2" x 12"	14-1/16"	14.1" Widescreen
PF15.0	9" x 12"	15"	15.0"
PF15.4W	8-3/16" x 13-1/16"	15-3/8"	15.4" Widescreen
PF15.6W	7-5/8" x 13-9/16"	15-9/16"	15.6" Widescreen
PF17.0	10-5/8" x 13-3/8"	17"	17.0"
PF17.0W	9-1/16" x 14-1/2"	17"	17.0" Widescreen
PF17.3W	8-1/2" x 15-1/16"	17-3/16"	17.3" Widescreen
PF18.1	11-3/8" x 14-1/8"	18-1/16"	18.1"

PF18.5W	9-1/16" x 16-1/8"	18-1/2"	18.5" Widescreen
PF19.0	11-7/8" x 14-13/16"	19"	19.0"
PF19.0W	10-1/8" x 16-3/16"	19"	19.0" Widescreen
PF20.1	12-1/8" x 16-1/8"	20-1/16"	20.1"
PF20.1W	10-3/4" x 17-1/8"	20-1/16"	20.1" Widescreen
PF21.3	12-13/16" x 18-5/8"	21-5/16"	21.3"
PF21.6W	11-7/16" x 18-1/4"	21-5/8"	21.6" Widescreen
PF22.0W	11-5/8" x 18-7/8"	22"	22.0" Widescreen
PF24.0W	12-3/4" x 20-3/8"	24"	24.0" Widescreen
PF26.0W	13-9/16" x 21-11/16"	26"	26.0" Widescreen
PF27.0W	14-3/8" x 22-15/16"	27"	27.0" Widescreen
PF28.0W	14-5/8" x 23-3/8"	28"	28.0" Widescreen
PF30.0W	15-3/4" x 25-3/16"	30"	30.0" Widescreen

Glass Framed Filter Sizes (Desktop LCD & CRT Monitors)	Filter Viewing Area Height X Width	Filter Viewing Area Diagonal	Fits Monitor Size
Large (L) (PF400L/LB, EF200L/LB, AF100L, EX10L)(Flat)	9-3/4" x 12-3/4"	16"	14"-16" CRT and 15" LCD
X-Large (XL, XLB)(flat)	11-1/2" x 14-1/8"	18-1/4"	16"-19" CRT and 17"-18" LCD
XX-Large (XXL,XXLB)(flat)	13 x 16	20-5/8"	19"-21" CRT and 19"-20" LCD